






## ARWEI-PREMIUM-REINSTREIFER DATA SHEET PORTAL NB 17 MIX 3/1

-  Static point loading up to 3,5 t per 80 cm<sup>2</sup>
-  Interior and roofed exterior
-  Suitable for wheelchairs
-  Coarse dirt absorption
-  Rollable


### Recommended for:

-  Private Homes
-  Office buildings
-  Schools

Height	Bar distance	Profile	Walking Area	Weight per m <sup>2</sup>
17 mm	4 / 6 mm	Aluminum	Needle felt, Three-way Brush	approx. 11,5 kg (with 6 mm bar spacing)

### System Design

- ① Needle felt
- ② ARWEI Three-way Brush
- ③ ARWEI special connector, without cable connections
- ④ Aluminum profile
- ⑤ Scratching Edge




### Characteristics

- High stability up to 3500 kg per 80 cm<sup>2</sup> static point load
- The ARWEI "Special Needle Felt" is certified "TÜV PROFiCERT-product Interior PREMIUM"

### Vorteile

- ARWEI-Premium-Reinstreifer is manufactured as a modular system.  
Every single part can be replaced easily on the spot.
- ARWEI needle felt convinces with an excellent cleaning effect, a duplicated life time versus conventional sling ware, a minimum of getting dirty itself and a high wear-resistance. 4-5 mm compact fabric top layer.
- The needle felt is fixed in a covered manner to prevent slipping sideways.
- The 3-way brushes on different levels improve the collection of coarse dirt.
- The special profile geometry of the ARWEI Reinstreifer allows for high strain, for example for driving over with wheel chairs and trolleys.

## Standard Colours



## Special Colours (Available at an extra charge)




Illustration of colors not true to original.  
On request you receive original samples promptly.  
Referring to needle felt colours. All brushes only in black available.

## Tender specifications: Portal NB 17 Mix 3/1

High quality, especially wear-resistant entrance mat, improved absorption of coarse dirt

**Application:** Indoor and roofed exterior; normal up to extremely strong frequency, suitable for trolley and wheelchairs, overall laying, Static point loading up to 3500 kg per 80 cm<sup>2</sup>

**Stripe profile:** aluminum, with scratching edge, sound insulated

**Cleaning pads:** Needle felt and brush, mix 3/1 (minimum 24 brush profiles each metre of walking depth)

**Needle felt special ground:** 100 % PP; pole density 2400 g/m<sup>2</sup>; completely needled; no sling ware, minimum contamination; extremely wear-resistant; is fixed in a covered manner to prevent slipping sideways; needle felt can be substituted subsequently; colours anthracite, light grey, grey blue; coconut, special colours on demand; slip resistance R 11 according to DIN 51130

**Brush:** ARWEI three-way brush; brushes on different levels for an improved absorption of coarse dirt, sound insulating, colour black, slip resistance R 13 according to DIN 51130


**Connection:** ARWEI Special Connectors; therefore easily to roll up, high slip resistance by anti-slip function; modular construction – no wire or cable connections -, each part can easily be replaced on the spot

**Height:** 17 mm

**Bar distance 4 mm:** needle felt walking area 54 cm and 25 brush profiles each m of walking depth

**Bar distance 6 mm:** needle felt walking area 52 cm and 24 brush profiles each m of walking depth

Angle frames in 20 x 20 x 3 mm are available in aluminum, brass or stainless steel.



ARWEI REINSTREIFER  
IN ACTION.

[www.youtube.com/arweitv](https://www.youtube.com/arweitv)



You Tube

Constructional and material changes in the course of further product development reserved. All dimensions are standard values without considering production engineering-related tolerances. They are based on our experience and testing. The variety of associated materials and working conditions that occur on jobsites are not checked in detail and cannot be influenced by us. The quality of your work depends on your own professional judgment and product usage. If in doubt of any application recommendation or instruction, conduct a small test or obtain technical advice. With the publication of this product data sheet invalidates all previous product information. The respective updated version of this datasheet can be found on our Homepage under [www.arwei.de](http://www.arwei.de).